




RIGHTWAY

MANUAL PHOROPTER

VT-6E

VT-6EL

Night mode Phoropter



Led light

Manual phoropter
VT-6E & VT-6EL
SPECIFICATION:

(A) Measuring range:

- (1)SPH: 0.00D~-19.00D(-0.25D)
0.00D~+16.75D(+0.25D)
- (2)CYL: 0.00D~-6.00D(-0.25D)
- (3)AX: 0°~180° (in 5° steps)
- (4)P.D: 50~78(in 1m/m steps)

(B) Auxiliary lenses:


- (1) Occluder: Occluder
- (2)Pinhole plate: pinhole plate(1mm)
- (3)P.D Check lens: P.D Check lens
- (4)Red/green filter: right eye:red; left eye:green
- (5)Polarizing filter: right eye 135°
- (6)Polarizing filter: left eye 45°
- (7)Lenses for retinoscope: +1.50D
- (8)Fixed cross cylinder lens: ±0.50D
- (9)Balance check: 6^Δ B/U dissociation prism
- (10)Balance check: 10^Δ B/I dissociation prism
- (11)Moddox rod: right eye red horizontal/vertical
- (12)Moddox rod: left eye white horizontal/vertical

(C) Cross cylinder lens(xc):

- cross cylinder lens: ±0.50D

(D) Rotary prism:

- Rotary prism: Rotary prism 0^Δ~20^Δ (in 1^Δ step)



Exclusive distributor:

Loyal Tech Company

Address: D11,1/F, Wah Mow factory Building,
5-7 Ng Fong Street, San Po Kong,
KLN.HONGKONG

Tel: 3563 9548

Fax: 3563 5256

Website: <http://www.loyaltech.com.hk>

Email: loyal.sales01@gmail.com